

COMPACT CHEMICAL OVERBOOTS



workMaster™
by RESPIREX

Petrochemical

Emergency Services

Industrial Chemicals

Hazardous Waste

Pharmaceuticals

A chemically protective front-opening anti-static overboot with a slip resistant sole.

- Chemically resistant Hazmax compound shaft and sole certified to EN 13832-3
- Conforms to EN 943-1 (Chemical protective clothing)
- Meets the requirements of NFPA 1991 (Chemical Vapour protection)
- Single piece injection moulded construction with integral moulded fastener ensures there are no seams or mounting/ fastener holes to leak
- No metal fasteners or components used in the construction, removing the potential for chemical corrosion
- Two button fitting allows adjustment for different calf sizes
- Kick off lug
- Slip resistant sole in yellow Hazmax compound
- Fuel and oil resistant shaft and sole
- CE marked on the shaft with date and year of manufacture
- REACH Compliant

Care

- Machine washable at up to 40°C
- Shelf life of over 10 years

Certification

Chemical Protective Footwear	EN 13832 pt 3
Safety Footwear	EN ISO 20347:2012 A FO SRC
Personal Protective Equipment	PPE DIR 89/686/EEC

Sizes

	Medium	Large	Extra-Large
UK	6 - 8	9 - 11	12 - 14
EU	39 - 42	43 - 45	46 - 49
US	7 - 9	10 - 12	13 - 15

EN 13832
Chemical
Protection



For use with safety shoes (safety shoes not included)

WORKMASTER™ CHEMICAL OVERBOOTS - CHEMICAL PERMEATION

Chemical	CAS no.	Method	Breakthrough time
Acetic acid (Glacial)	64-19-7	EN374-3	Over 8 HOURS
Acetone	67-64-1	EN374-3	Over 2 HOURS
Acetone Cyanohydrin	75-86-5	EN374-3	Over 8 HOURS
Acetonitrile	75-05-08	EN374-3	Over 6 HOURS
Acrylic Acid	79-10-7	EN374-3	Over 8 HOURS
Acrylonitrile	107-13-1	EN374-3	Over 2 HOURS
Ammonia 5%	1336-21-6	EN374-3	Over 8 HOURS
Ammonia Gas	7664-41-7	EN374-3	Over 8 HOURS
Ammonium Pentadecafluoro-octanoate (30% in water)	3825-26-1	EN374-3	Over 8 HOURS
Aniline	62-53-3	EN374-3	Over 8 HOURS
Anti-knock(Tetraethyl lead 60%Dibromoethane 30%/ Dichloroethane 10% TEL-CB	78-00-2 / 106-03-4 / 107-06-2	EN374-3	Over 8 HOURS
Aqueous Phenol 85%	108-95-2	EN374-3	Over 8 HOURS
Arsenic Acid	7778-39-4	EN374-3	Over 8 HOURS
Benzene	71-43-2	EN374-3	Over 4 HOURS
Benzene 85.5%/Toluene 8.6%/ Xylene3.2%/ Naphalene2.7%		EN374-3	Over 3 Hours Benzene only
Benzyl Chloride	100-44-7	EN374-3	Over 8 HOURS
Bromine	7726-95-6	EN374-3	Over 7 HOURS
Buta-1,3-diene Gas	106-99-0	EN374-3	Over 3 HOURS
Butyl Acetate	123-86-4	EN374-3	Over 6 HOURS
Cable oil		EN374-3	Over 8 HOURS
Carbazole	86-74-8	EN374-3	Over 8 HOURS
Carbon Disulphide	75-15-0	EN374-3	Over 1 HOUR
Chlorine Gas	7782-50-5	EN374-3	Over 3 HOURS
Chromic Acid	1333-82-0	EN374-3	Over 8 HOURS
Cyanogen Chloride	506-77-4	NFPA	No permeation detected
Cyclohexylamine	108-91-8	EN374-3	Over 8 HOURS
Dichloromethane	75-09-02	EN374-3	Over 1 HOUR
Diethylamine	109-89-7	EN374-3	Over 2 HOURS
Diethylene Glycol dimethylether	111-46-6	EN374-3	Over 8 HOURS
Dimethyl Formamide	68-12-2	EN374-3	Over 8 HOURS
Epichlorohydrin	106-89-8	EN374-3	Over 7 HOURS
Ethanol (Ethyl Alcohol)	64-17-5	EN374-3	Over 8 HOURS
Ethyl Acetate	141-78-6	EN374-3	Over 4 HOURS
Ethylene Glycol	107-21-1	EN374-3	Over 8 HOURS
Ethylene Dichloride	107-06-2	EN374-3	Over 8 HOURS
Ethylene Oxide	75-21-8	EN374-3	Over 2 HOURS
Ethylenediamine tetra-acetic acid tetrasodium salt(EDTA) 5%	64-02-8	EN374-3	Over 8 HOURS
Formaldehyde 37 %	50-00-0	EN374-3	Over 8 HOURS
Formic Acid 65%	64-18-6	EN374-3	Over 8 HOURS
Hexane	110-54-3	EN374-3	Over 7 HOURS
Hydrazine	302-01-2	EN374-3	Over 8 HOURS
Hydrazine 5%	7803-57-8	EN374-3	Over 8 HOURS
Hydrochloric Acid 48%	7647-01-0	EN374-3	Over 8 HOURS
Hydrofluoric Acid 48%	7664-39-3	EN374-3	Over 8 HOURS
Hydrofluoric Acid 48%	7664-39-3	EN374-3	Over 66 HOURS
Hydrofluoric Acid 73%	7664-39-3	EN374-3	Over 8 HOURS
Hydrogen Chloride Gas	7647-01-0	EN374-3	Over 8 HOURS

Chemical	CAS no.	Method	Breakthrough time
Hydrogen Fluoride gas anhydrous	7664-39-3	EN374-3	Over 1 HOUR
Hydrogen Peroxide (10 volume (3%) solution)	7722-84-1	EN374-3	Over 8 HOURS
Hydrogen Peroxide (50%)	7722-84-1	EN374-3	Over 8 HOURS
Iso-butane	75-28-5	EN374-3	Over 8 HOURS
Iso-butane followed by Hydrofluoric acid 71-75%	75-28-5 + 7664-39-3	EN374-3	Over 8 HOURS
Iso-propanol (IPA)	67-63-0	EN374-3	Over 8 HOURS
Lewisite	541-25-3	NFPA	No permeation detected
m-Cresol	108-39-4	EN374-3	Over 8 HOURS
Methanol	67-56-1	EN374-3	Over 8 HOUR
Methyl Ethyl Ketone (M.E.K) 2-Butanone	78-93-3	EN374-3	Over 2 HOURS
Methyl Iodide 99%	74-88-4	EN374-3	Over 1.5 HOURS
Methyl Methacrylate	80-62-6	EN 369	Over 3 HOURS
methyl-1,2-pyrrolidone	872-50-4	EN369	Over 8 HOURS
Methylene Chloride Gas	74-87-3	EN374-3	Over 1 HOUR
Monochloroacetic acid	79-11-8	EN374-3	Over 8 HOURS
Mustard Gas	505-60-2	NFPA	No permeation detected
Naphalene	91-20-3	EN374-3	Over 8 HOURS
N,N-Dimethylaniline	121-69-7	EN374-3	Over 8 HOURS
N,N-dimetyl acetamide	127-19-5	EN374-3	Over 8 HOURS
Nitric Acid 50%	7697-37-2	EN374-3	Over 8 HOURS
Nitric Acid 70% conc	7697-37-2	EN374-3	Over 8 HOURS
Nitric Acid Etchant 80/20	7697-37-2	EN374-3	Over 8 HOURS
Nitro Benzene	98-95-3	EN374-3	Over 3 HOURS
Oleum 40% SO ₃	8014-95-7	EN374-3	Over 8 HOURS
Oxalic Acid saturated solution	6153-56-6	EN374-3	Over 8 HOURS
Phenol 50% in Methanol	108-95-2/67-56-1	EN374-3	Over 8 HOURS
Phosphoric acid 25%	7664-38-2	EN374-3	Over 8 HOURS
Phosphoric acid 75%	7664-38-2	EN374-3	Over 8 HOURS
Propylene 1,2 oxide	75-56-9	EN374-3	Over 1 HOUR
Red Fuming Nitric acid	7697-37-2	EN374-3	Oner 4 HOURS
Saren Gas	107-44-8	NFPA	No permeation detected
Sodium Cyanide 30wt%	143-33-9	EN374-3	Over 8 HOURS
Sodium Hydroxide 40%	1310-73-2	EN374-3	Over 8 HOURS
Sodium Hypochlorite 16%	7681-52-9	EN374-3	Over 8 HOURS
Styrene	100-42-5	EN374-3	Over 8 HOURS
Sulphuric Acid 96%	7664-93-9	EN374-3	Over 8 HOURS
Tetrachloroethylene	127-18-4	EN374-3	Over 3 HOURS
Tetraethyl Lead (Octel Anti Knock)	78-00-2	EN374-3	Over 8 HOURS
Tetrahydrofuran	109-99-9	EN374-3	Over 3 HOURS
Toluene	108-88-3	EN374-3	Over 4 HOURS
Toluene 2,4 Diisocyanate	584-84-9	EN374-3	Over 8 HOURS
Trichloroethane	71-55-6	EN374-3	Over 6 HOURS
Trichloroethylene 1,1,2	79-01-6	EN374-3	Over 3 HOURS
Triethanol-amine	102-71-6	EN374-3	Over 8 HOURS
Triethylene Glycol	112-27-6	EN374-3	Over 8 HOURS
Trigonox K-80 Cumyl hydroperoxide 80% / 20% Cumene	80-15-9/ 98-82-8	EN 369	Over 8 HOURS
VX	50782-69-9	NFPA	No permeation detected
Xylene	1330-20-7	EN374-3	Over 4 HOURS