

# MaxiFlex®

PRECISION HANDLING™



Tested for harmful substances.  
www.oeko-tex.com/standard100

## USE (MECHANICAL PROTECTION)

**Mechanical work glove for PRECISION HANDLING™ in dry environments.**  
Performance levels relate to the palm area of the glove

**No protection against liquids or chemicals. Do not use these gloves to protect against serrated edges or blades or naked flames. MaxiFlex® shall not be worn when there is a risk of entanglement by moving parts or machines.**

If gloves are required for heat applications be sure that the glove conform to EN407 and that is tested in accordance with your requirements. Before use, inspect the gloves for any defects or imperfections and avoid wearing damaged, heavily soiled, worn or dirty (also internally) glove of any substance, this could irritate and/or infect the skin and cause dermatitis. In this event, seek medical advice from the company doctor or consult a dermatologist. After use, clean the gloves thoroughly with a dry cloth to remove any contaminants. If the gloves are to be re-worn store in such a way that the inside lining of the support can dry out easily.

### Sizing according to EN 420:2003

Size	Minimum length (mm)	Palm circumference (mm)
5 (EU) XXS (US)	210 mm	137 mm
6 (EU) XS (US)	220 mm	152 mm
7 (EU) S (US)	230 mm	178 mm
8 (EU) M (US)	240 mm	203 mm
9 (EU) L (US)	250 mm	229 mm
10 (EU) XL (US)	260 mm	254 mm
11 (EU) XXL (US)	270 mm	279 mm
12 (EU) XXXL (US)	280 mm	295 mm

For ergonomic reasons our gloves may be shorter than the standard specification set out in the legislation which is done to ensure flexibility of the wrist and subsequently only protect the hand and not the wrist or forearm. They are therefore suitable only for specific applications.

## EXPLANATION OF THE PICTOGRAMS

	<b>EN 420:2003+A1 2009</b> General requirements (risk category, sizing, marking, labelling, etc.) Information supplied by the manufacturer in the user notice
 A B C D E F	<b>EN 388:2016</b> Mechanical Hazards A: Abrasion resistance - number of rubs (Level 0-4) B: Blade cut resistance - Coupe Test - Index (Level 0-5) C: Tear resistance - N (Level 0-4) D: Puncture resistance N (Level 0-4) E: TDM Cut resistance according to ISO 13997 - N (Level A-F)* F: Impact protection according to EN 13594:2015 - Y/N (P=Yes)
 ABCD	<b>EN 388:2003</b> Mechanical Hazards A: Abrasion resistance - number of rubs (Level 0-4) B: Blade cut resistance - Coupe Test - Index (Level 0-5) C: Tear resistance - N (Level 0-4) D: Puncture resistance N (Level 0-4)
 A B C D E F	<b>EN 407: 2004 / MaxiFlex® Comfort™, MaxiFlex® Cut™ 34-1743)</b> Thermal Hazards (Heat/Fire) A: Flammability (0-4) B: Contact heat (0-4) C: Convective heat (0-4) D: Radiant heat (0-4) E: Small splashes of molten metal (0-4) F: Large quantities of molten metal (0-4)
	<b>Food Contact</b> Sign shows suitability for direct or indirect food contact. Please visit <a href="http://www.atg-glovesolutions.com">www.atg-glovesolutions.com</a> to determine the suitability by food.
	<b>Production date (EU)</b> MM/YYYY

Higher values stand for better protection/resistance. If "X" is marked as a performance level the test is either not applicable or not proceeded. Puncture resistance should not be confused with piercing exerted by thin tips or needles.  
\* COUPE TEST RESULTS ARE ONLY INDICATIVE WHILE THE TDM CUT RESISTANCE TEST (ISO13997) IS THE REFERENCE PERFORMANCE RESULT.

## CONSTITUENTS / ALLERGIES

Some gloves may contain ingredients which are known to be a possible cause of allergies in sensitive persons who may develop irritant and/or allergic contact reactions. If an allergic reaction should occur seek medical advice immediately.  
**WARNING – THIS PRODUCT MAY CONTAIN NATURAL LATEX WHICH MAY CAUSE AN ALLERGIC REACTION; FOR MORE INFORMATION PLEASE CONTACT ATG@TECHNICAL DEPARTMENT.**

## CARE INSTRUCTIONS

### Storage/Cleaning:

Store the gloves in their original packaging in a cool and dry place.  
Keep away from direct sunlight, heat, flame and sources of Ozone.  
Gloves can be laundered at 40°C with a standard detergent (3 cycles), Natural drying.  
(EU) - Gloves can be used out of the pack 5 years after production date, printed on the glove.  
Gloves should be used within 3 years after their purchase.  
Glove life time in use is based on wear and abrasion.

### Disposal/Waste:

Used gloves may be contaminated with infectious or hazardous substances, dispose of according to the Local Authority/Municipality Regulations, landfill or incinerate under controlled conditions. For more information on glove selection, usage and performances and for a copy of the CE declaration of conformity please contact ATG@ (info@atg-glovesolutions.com or send a fax to: +94-11-225.38.87) or the supplier of these gloves.

## WARRANTY/LIMITATION OF DAMAGES

ATG® warrants that this product shall be in accordance with ATG® standard specifications as of the date of delivery to authorized distributors. Except to the extent prohibited by law, this warranty is in line with all warranties, including any warranty of fitness for a particular purpose; ATG® liability shall be limited to the purchase price of the product at issue. Buyers and users of this product are deemed to have accepted the terms of this limitation of warranty, which may not be varied by any verbal or written agreement.