



## 70G 12" Qualatherm 450 Wet/Dry Thermal Protection

## **ESD Technical Bulletin**



Electrostatic Decay in Combination with a Person		
Standard:	Rate of decay shall be less than 2.0 sec- onds @12%RH	
Found:	+1kV to -100V Ave: >2.0 sec1kV to -100V Ave: >2.0 sec.	
Method:	Mil-STD-3010C, 4046 (Modified) @49.5%RH	

Café Glove with a Pers	Resistance in Combination	R
Target:	Less than 1.0 x $10^{11}$ ohms @ 12%RH and 50%RH	F
Range:	Min: $2.1 \times 10^{12}$ ohms Max: $2.1 \times 10^{13}$ ohms	
Method:	ANSI/ESD SP15.1 @49.5%RH for 48 Hours	

ESD Inside Shelf Life		
<b>Requirement:</b>	3 Years	
Found:	Indefinite for Storage	
<b>Reference:</b>	Contains no Antistats	

## **Surface Resistance**

Target:	$1.0 \times 10^{11}$ ohms and greater at $12\% RH$
Range:	Min: 3.7 x 10 <sup>10</sup> ohms Max: 7.1 x 10 <sup>10</sup> ohms
Method:	ANSI/ESD STM11.11-2015 @ 10.1%RH for 48 Hours

Volume Resistance		
Standard:	Less than 1.0 x 10 <sup>11</sup> ohms @12%RH	
Range:	Min: $5.5 \times 10^{11}$ ohms Max: $2.5 \times 10^{12}$ ohms	
Method:	ANSI/ESD STM11.12-2015 @ 49.5%RH for 48 Hours	

Product Recommendations: The information presented herein is not guaranteed in any way, although to the best of QRP's knowledge and belief, it is true and accurate as of this date. Because the manner and conditions of use, handling, storage and other factors may involve a variety of safety, performance, or regulatory considerations unknown to QRP, users are responsible for determining the suitability of any QRP product for their specific purpose. QRP, Inc. does not warrant the results to be obtained in using any QRP product, and disclaims all liability with respect to the use, handling or further processing of any such product.

rev: 28Sept2016

QRP Inc. 3781 N. Highway Drive Tucson, AZ 85705 USA Phone: 800.832.3882 • 520.790.3533 Email: info@qrpgloves.com • Web: www.qrpgloves.com