

Safetyware

SAFETYWARE GROUP

Responsibility & Care



**EMERGENCY
EYEWASH & SHOWER**



ESE1000FSS

ESE1001FSS



Full Stainless Steel Floor Mounted Emergency Shower & Eyewash Combination

Item Code	Type	Unit
ESE1000FSS	Without Foot Pedal	EA
ESE1001FSS	With Foot Pedal	EA

- Shower head delivers 76 liters of water per minute. Large area covers water flow at 60", the water pattern covers 20" in diameter. Center of the water pattern is 16" from any obstructions
- Eye wash delivers 11.5 liters of water per minute. Dust cover protects spray heads from airborne particulates and other contaminants
- Ball valve is activated in one second or less
- Hands-free stay-open valve activates in one second
- Easily located, accessible actuator is not higher than 69" above floor
- Comply to EN15154-1&2, ANSI Z358-1 and AS4775 Safety Standard



ESE3000FSS

ESE3001FSS



Full Stainless Steel Floor Mounted Emergency Eyewash

Item Code	Type	Unit
ESE3000FSS	Without Foot Pedal	EA
ESE3001FSS	With Foot Pedal	EA

- Eye wash delivers 11.5 liters of water per minute. Dust cover protects spray heads from airborne particulates and other contaminants
- Controlled low-velocity flow completely rinses eyes and face
- Ball valve is activated in one second. Valve actuator is easily located and readily accessible to user
- Hands-free open valve activates in one second
- Easily located, accessible actuator is not higher than 69" above floor
- Comply to EN15154-1&2, ANSI Z358-1 and AS4775 Safety Standard



Full Stainless Steel Wall Mounted Emergency Shower

Item Code	Unit
ESE4000FSS	EA

- Provide good performance and durability, with ease of installation and maintenance
- Emergency showers are rod operated
- Meets ANSI Z358.1 and EN15154-1&2 Safety Standard



Full Stainless Steel Wall Mounted Emergency Eyewash

Item Code	Unit
ESE5000FSS	EA

- Eyewasher delivers 11.5 liters of water per minute. Dust cover protects spray heads from airborne particulates and other contaminants
- Controlled low-velocity flow completely rinses eyes and face
- Ball valve is activated in one second. Valve actuator is easily located and readily accessible to user
- Hands-free open valve activates in one second
- Comply to EN15154-1&2, ANSI Z358-1 and AS4775 Safety Standard



Decked Mounted Pull Out Eye Washer

Item Code	Unit
ESE6000SS	EA

- Main body : Chrome plated forged brass
- Valve : Brass squeeze valve actived by stainless steel 304 lever handle
- Sprayer : 1 spray head with rubber dust cover
- Hose : 1.5 meters long
- Water working pressure : 0.2MPA-0.8MPA
- Supply : 1/2" IPS/NPT
- Meets ANSI Z358.1 and EN15154-1&2 Safety Standard



Decked Mounted Pull Out Eye Washer

Item Code	Unit
ESE6001SS	EA

- Main body : Chrome plated forged brass
- Valve : Brass squeeze valve actived by stainless steel 304 lever handle
- Sprayer : 2 spray heads with rubber dust cover
- Hose : 1.5 meters long
- Water working pressure : 0.2MPA-0.8MPA
- Supply : 1/2" IPS/NPT
- Meet ANSI Z358.1 and EN15154-1&2 Safety Standard



Faucet - Mounted Eye Washer

Item Code	Unit
ESE7000	EA

- Convert any faucet into an emergency eyewash station without interfering with normal faucet operation
- It is easy to install and can be activated quickly
- The main body is made by chrome plated forged brass



Full Stainless Steel Decontamination Eyewash Station

Item Code	Unit
ESE8001FSS	EA

- Piping Material & Eyewash Bowl: Stainless Steel 304
- Eyewash Valve: 1/2" Stainless Steel 304 ball valve
- Water Supply: 1/2" IPS; Water Outlet: 1-1/4" IPS
- Flow Control: 12L/Min
- Water Working Pressure: 0.2-0.8MPA
- Assist to flush hazardous contaminants and irritants from eyes and facial area
- Include a push handle and foot pedal to activate the eyewash
- Automatic anti-dust cover which operates when the eyewash is used
- Comply to EN 1514-1 & 2 and ANSI Z358.1 Safety Standard



Full Stainless Steel Decontamination Shower Station

Item Code	Unit
ESE8002FSS	EA

- Piping Material: Stainless Steel 304
- Shower Valve: 1-1/4" Stainless Steel 304 ball valve
- Water Supply: 1-1/4" IPS
- Flow Control: 76L/Min
- Water Working Pressure: 0.2-0.8MPA
- Assist in the rapid removal of contaminants from the body with a deluge of flushing fluid
- Shower station is activated by entering the platform
- Comply to ANSI Z358.1 Safety Standard



Full Stainless Steel Decontamination Eyewash & Shower Station

Item Code	Unit
ESE8003FSS	EA

- Piping Material & Eyewash Bowl: Stainless Steel 304
- Shower Valve: 1-1/4" Stainless Steel 304 ball valve
- Eyewash Valve: 1/2" Stainless Steel 304 ball valve
- Water Supply/Outlet: 1-1/4" IPS
- Shower Flow Control: 76L/Min
- Eyewash Flow Control: 12L/Min
- Water Working Pressure: 0.2-0.8MPA
- Assist in the rapid removal of contaminants from the body with a deluge of flushing fluid together with an eyewash station to flush hazardous contaminants and irritants from eyes and facial area
- Shower station is activated by entering the platform. While eyewash station is activated by push handle and foot pedal
- Comply to EN 1514-1 & 2 and ANSI Z358.1 Safety Standard



Emergency Eyewash Bottle

Item Code	Dimension (WxH)	Material	Packing	Unit
EPE01	70mm x 210mm	PE	25pcs/ Inner Box	EA

- Portable and easy to use
- Capacity 300ml
- Perfect for flushing particles such as pollen, dust, sawdust, smoke, etc



EPE08

EPE16

Portable Emergency Eyewash

Item Code	Colour	Dimension (LxWxH)	Capacity	Unit
EPE08	Bright Green	555mm x 255mm x 370mm	8 Gallons/ 30 Litres	EA
EPE16	Bright Green	546mm x 495mm x 572mm	16 Gallons/ 60.5 Litres	EA

- Made of non-toxic Polyethylene (PE)
- Wide-fill opening & threaded cap for quick inspection, cleaning and filling
- Come with mounted operating instruction
- Gravity fed supply, no plumbing required
- 10 minutes continual flow (EPE08); 15 minutes continual flow (EPE16)
- It is suggested to change water every 90 days





Stainless Steel Shower Rail

Item Code	Size	Thickness	Material	Unit
EESR966	966mm	1.2mm Thick c/w Support Brace	SUS 304	EA

- Used for hanging shower curtain



Shower Curtain

Item Code	Colour	Dimension (LxH)	Ring Material	Unit
ESESCW18	Transparent	1800mm x 2000mm	Stainless Steel	EA

- Minimize the spray and the possibility of equipment damage when using emergency shower
- Designed to be used in combination emergency drench shower and eyewash units
- With a quick sweep of the hand on both sides, the curtain wraps around to enclose the shower and user



ESEP650SS



ESEP100SS



ESEP150SS



ESEP550SS



ESEP600SS

Item Code	Description	Unit
ESEP650SS	Central Eyewash Sprayer set	EA
ESEP100SS	Eyewash Bowl	EA
ESEP150SS	Shower Head	EA
ESEP550SS	316 Eyewash Ball Valve 1/2"	EA
ESEP600SS	316 Shower Ball Valve 1"	EA